





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

#4-40 UNC






-, MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

-, SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C ~ +105° C.

✱【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. ADP-0W2S-25P	TITLE: DP25F 插板铆鱼叉锁螺丝		
X.X:±0.25	X.X':±2°		MANUFACTURE DWG		
X.XX:±0.05	X.XX':±1°				
UNITS	mm	DESIGN: Ethan	 SCALE N:A SHEET 1/1		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			