






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




一、 MATERIAL:

1. Insulator: PBT+30%Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Glod Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

二、 SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C~+105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



RECOMMEND PCB LAYOUT (T=1.6)
PCB TOLERANCE: ±0.05

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5°	PART NO. ADR-0B3C-37P	TITLE: DR37F 叉锁	
X.X:±0.25	X.X':±2°		MANUFACTURE DWG	
X.XX:±0.15	X.XX':±1°			
UNITS	mm	DESIGN: Ethan	 SCALE N:A	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SHEET	1/1