






| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |




#### → MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

#### → SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100MΩ MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55°C~+105°C.

✱ 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

| TOLERANCE  |             |  深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                     |                                                                                                    |     |
|------------|-------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|----------------------------------------------------------------------------------------------------|-----|
| X.:±0.30   | X':±1"      | PART NO.<br>AHDB-0B1H-15P                                                                                                                                | TITLE:<br>HDB15F 铆合 | MANUFACTURE DWG                                                                                    |     |
| X.X:±0.25  | X.X':±0.5"  |                                                                                                                                                          |                     |                                                                                                    |     |
| X.XX:±0.15 | X.XX':±0.1" |                                                                                                                                                          |                     |                                                                                                    |     |
| UNITS      | mm          | DESIGN:                                                                                                                                                  | Ethan               |  SCALE<br>N:A |     |
| MATERILA   | — — —       | CHED:                                                                                                                                                    | Olvia               |                                                                                                    |     |
| FINISH     | — — —       | APPD:                                                                                                                                                    | Ava                 |                                                                                                    |     |
|            |             |                                                                                                                                                          |                     | SHEET                                                                                              | 1/1 |