




- SPECIFICATIONS
- 1、Current Rating: 3A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -40℃~ +105℃
 - 4、Contact Resistance: 10mΩ Max
 - 5、Insulation Resistance: 1000mΩ Min
 - 6、Withstanding Voltang: 1500V AC/minute
 - 7、Material: Phosphoric bronze Tin-platde
 - 8、Applicable Wire Sizes:AWG#26~20#

TYPE	Dimension mm				适用线规
	A1	B1	A2	B2	AWG#
HC-XHM-T-05	2.15	2.0	1.4	1.5	26-24
HC-XHM-T-B-05(高脚)	2.35	2.0	2.0	2.2	22-20

			GENERL TOLERANCE	制 图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK				
			X.X ±0.30	批 准 APPROVAL				
1	初版发行		X.XX ±0.20	比 例 SCALE	产品名称 TITLE	XHM (2.50) 端子	版 本 REV.	A
			X.XXX ±0.10	投 影 Projection	产品料号 PART NO.	HC-XHM-T-05	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°		材 料 MATERIAL		页 次 SHEET	1/1