

Technical drawing of a mechanical part showing dimensions: 3.4 ± 0.25 , 1.2 ± 0.25 , and 1.2 .

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{m}\Omega$ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0(2)
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2x2	HC-PAB-2x2AS-05	2.00	6.00
2x3	HC-PAB-2x3AS-05	4.00	8.00
2x4	HC-PAB-2x4AS-05	6.00	10.00
2x5	HC-PAB-2x5AS-05	8.00	12.00
2x6	HC-PAB-2x6AS-05	10.00	14.00
2x7	HC-PAB-2x7AS-05	12.00	16.00
2x8	HC-PAB-2x8AS-05	14.00	18.00
2x9	HC-PAB-2x9AS-05	16.00	20.00
2x10	HC-PAB-2x10AS-05	18.00	22.00
2x11	HC-PAB-2x11AS-05	20.00	24.00
2x12	HC-PAB-2x12AS-05	22.00	26.00
2x13	HC-PAB-2x13AS-05	24.00	28.00
2x14	HC-PAB-2x14AS-05	26.00	30.00
2x15	HC-PAB-2x15AS-05	28.00	32.00
2x16	HC-PAB-2x16AS-05	30.00	34.00
2x17	HC-PAB-2x17AS-05	32.00	36.00
2x18	HC-PAB-2x18AS-05	34.00	38.00
2x19	HC-PAB-2x19AS-05	36.00	40.00
2x20	HC-PAB-2x20AS-05	38.00	42.00


HC-PAB - N*** - * - ** - 05

Pin Type Colour Contact Plating

Y-乳白
AS-直封塑料

默认-本色
默认-红色

默认-Tin Plating (镀锡)
默认-Gold Plating (镀金)



			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO., LTD				
			DIM TOL	审 核 CHECK					
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	PAB (2.0) 双排 带扣 直针 带柱	版 本 REV.	A
			X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	HC-PAB-2xNAS-05	单 位 UNITS	mm
1	初版发行		X.XXX ±0.10						
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1