





1. MATERIAL:
HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, BLACK COLOR,
CONTACTS: COPPER ALLOY.
PEGS: COPPER ALLOY.

2. FINISH:
CONTACTS: SELECTED GOLD PLATING ON THE CONTACT AREA,
1u" MIN. GOLD PLATING ON THE SOLDERTAILS,
50 u" MIN. NICKEL UNDERPLATING OVER ALL.
PEGS: 120u" MIN. MATTE-TIN OVER 50u" MIN. NICKEL.

CURRENT RATING : 0.5A 50V AC/DC
CONTACT RESISTANCE : 55 mΩ MAX
INSULATION RESISTANCE : 500 MΩ MIN AT 500V DC
OPERATING TEMPERATURE : -55°C~80°C



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±5°	PART NO. A052R2-52H	TITLE: 0.80MM PITCH MINPCIEXPRESS HIGH=5.2mm 52 PIN CONNECTOR		
X.X:±0.25	X.X':±1°				
X.XX:±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava		SCALE N:A	SHEET 1/1