







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



→ MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Glod Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated


→ SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100MΩ MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

※【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

RECOMMEND PCB LAYOUT (T=1.6)

PCB TOLERANCE:±0.05

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.:±0.30	X':±5"	PART NO. ADR-1B2C-37P	TITLE: DR37M叉锁	
X.X:±0.25	X.X':±2"		MANUFACTURE DWG	
X.XX:±0.15	X.XX':±1"			
UNITS	mm	DESIGN: Ethan	 SCALE N:A	
MATERILA	— — —	CHED: Olvia		
FINISH	— — —	APPD: Ava		
			SHEET	1/1