





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05


— MATERIAL:


1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

— SPECIFICATION:

1. Current Rating: 3 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: -55° C ~ $+105^{\circ}$ C.

✱ 【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.: ± 0.30	X': $\pm 1^{\circ}$	PART NO. ADP-1B1H-15P	TITLE: DP-15M 铆合	MANUFACTURE DWG	
X.X: ± 0.25	X.X': $\pm 0.5^{\circ}$				
X.XX: ± 0.05	X.XX': $\pm 0.1^{\circ}$				
UNITS	mm	DESIGN:	Ethan		
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		
					SCALE N:A
					SHEET 1/1