






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




➤ MATERIAL:

- 1.Insulator:PBT+30%Glass Fiber
- 2.Contact:Brass
- 3.Contact Plated:Gold Flash over Tin Or Gold Plated Or Tin Plated
- 4.Shell:Steel,Nickel Plated

➤ SPECIFICATION:

- 1.Current Rating:3 AMPS
- 2.Insulation Resistance: 100MΩ MIN. At 500VDC
- 3.Dielectric Strength: 500V for One minute
- 4.Operation Temperature: -55° C~+105° C.

✳️【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.30	X':±1"	PART NO. ADB-0W3H-9P	TITLE: DB9M 铆合		
X.X:±0.25	X.X':±0.5"				
X.XX:±0.15	X.XX':±0.1"		MANUFACTURE DWG		
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1