

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀金0.8u"MIN

Contact: Brass, 0.8u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/minute.

温度范围: -40° C to +105° C


Temperture Range: -40° C to +105° C



Ordering Information

B190-1 XX XX X S X X X

NO. OF PINS	Contact Plating	INSULATOR	BACK	PACKING
6-64P	Full of Gold	Series-gold	MATERIAL:	
A0=0.8u"	B0=0.8u"	A: PBT	G: Grey427	A: PE Bag
A1=1u"	B1=1u"	B: PA6T	E: Grey413	B: Tape & Reel
A2=1.5u"	B2=1.5u"	C: PA9T	W: White	C: Tube
A3=2u"	B3=2u"	D: LCP	U: Blue	D: Tube+CAP
A4=3u"	B4=3u"			E: Tray
A5=5u"	B5=5u"			
A6=10u"	B6=10u"			
A7=15u"	B7=15u"			
A8=20u"	B8=20u"			
A9=30u"	B9=30u"			
S1=Q di nary Tin Plated				
S2=Matte Tin Plated				
S3=Tin-plated High-temperature				



RoHS
COMPLIANT

注
意
事
项

1. 带*为品质重点检验尺寸

				OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.	
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	刘伟 2021.06.15	PART NO.	B190-1XXXXXXSXXX
				X.XXX	±0.10						
A0	2021.06.15	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE:	2.54筒牛 塑高9.0 XXP 180度 DIP:3.0
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	

Yxcon 东莞市宇熙精密连接器有限公司
Dongguan Yuxi Electronic Co., Ltd.