








NOTES:

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: COPPER ALLOY, T=0.35.
3. PLATING: GOLD PLATED ON CONTACT AREA, 100u"MIN. MATTE TIN PLATED ON SOLDERING AREA, 50u"MIN. NICKEL PLATED OVERALL.
4. SHELL: COPPER ALLOY, T=0.20. 40u"MIN. NICKEL PLATED OVERALL.
5. LED: T=0.50, MATE TIN PLATED.

ELECTRICAL:

1. VOLTAGE RATING: 125V AC RMS.
2. CURRENT RATING: 1.5AMP.
3. CONTACT RESISTANCE: 40MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500MEGOHMS MIN @100V DC.

MECHANICAL:

1. DURABILITY: 750 CYCLES MIN.
2. INSERTION FORCE: 22N MAX.
3. REMOVAL FORCE (WITHOUT PLUG LOCK): 22N MAX.



ENVIRONMENTAL:

1. STORAGE: -40°C~85°C
2. OPERATION: -40°C~85°C

*Apply to the EU standards (ROSH)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明



PCBLAYOUT
TOL: ±0.05

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.: ±0.35	X': ±3"	PART NO. RJ45-3014-8P	TITLE: RJ45 沉板 3.0 带弹 带灯	
X.X: ±0.25	X.X': ±2"		MANUFACTURE DWG	
X.XX: ±0.15	X.XX': ±1"			
UNITS	mm	DESIGN:	Ethan	
MATERIAL	— — —	CHED:	Olvia	
FINISH	— — —	APPD:	Ava	
				SCALE N:A
				SHEET 1/1