






PCB.焊接图
PCB.WELDING DRAWING



电路图
CIRCUIT DIAGRAM



NOTES:

- 1.Rating:12VDC 50mA
1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC
2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max
3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
4.绝缘电阻: ≥100MΩ
- 5.Operating Force:160±50gf
5.操作力: 160±50gf
- 6.Life: 30,000 times
6.寿命: 30,000 次
- 7.Travel:0.20±0.10mm
7.行程: 0.20±0.10mm
- 8.Operating Temperature: -20℃~80℃
8.工作温度: -20℃~80℃

5	Button 按钮	PPA	1	white 白色
4	Cover plate 盖板	SUS	1	
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Body 本体	PAA	1	Black 黑色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
MODEL NO: TP13621625			
Https: www.rocpcu.tw			
ROPCU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			