



技术要求 Specification:

- 2、额定电流Current rating: 5A max
 - 3、额定电压 Voltage rating: 250V AC/DC
 - 4、温度范围 Temperature range: -25°C to +85°C
 - 5、接触电阻 Contact resistance: $\leq 15\text{m}\Omega$
 - 6、绝缘电阻 Insulation resistance: $\geq 1000\text{M}\Omega$
 - 7、耐压 Withstand voltage: 1000V AC/minute
 - 8、插针的固定力 Fixing force of pins: $\geq 25\text{N}$
 - 9、适配的插头 Adaptable plug: HX30001-P(43645-P)
 - 10、适用基板厚度 Applicable PC board thickness: 1.6mm
 - 11、产品无严重损伤、缺针、长短针、旋转针等缺陷;

插针镀层无脱落、起皮、发黄等缺陷。

The product has no defects such as serious injury, lack of needle, long needle and rotating needle.

The coating of the pin has no defects such as abscission, peeling and oxidizable.

C	9.0	12.0	15.0	18.0	21.0	24.0	27.0	30.0	33.0	36.0	39.0
B	9.7	12.7	15.7	18.7	21.7	24.7	27.7	30.7	33.7	36.7	39.7
A	3.0	6.0	9.0	12.0	15.0	18.0	21.0	24.0	27.0	30.0	33.0
孔数	2	3	4	5	6	7	8	9	10	11	12