

Ordering Information

1. 材料(MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0,Color: Black

四方针：黄铜，镍底30 μ "MIN, 表面镀金0.8 μ "MIN

Contact: Brass, 0.8u"MIN GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current: 2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

缘阻抗: 1000 MΩ MIN.





Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V.

Withstanding Voltage: AC 500V.

温度范围: -40°C to $+105^{\circ}\text{C}$

Temperature Range: -40°C to $+105^{\circ}\text{C}$



P220-12 05 A0 A S 08

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Pin to Pin	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
10: 1.0mm	2~40P	Full of Gold	A: PBT		A: PE Bag
15: 1.5mm		A0=0.8u"	B: PA6T		B: Tape & Reel
20: 2.0mm		A1=1u"	C: PAGT		C: Tube
		A2=1.5u"	D: LCP		D: Tube+CAP
		A3=2u"			E: Tray
		A4=3u"			
		A5=5u"			
		A6=10u"			
		A7=15u"			
		A8=20u"			
		A9=30u"			
		S1=Q di nary Tin Plated			
		S2=Matte Tin Plated			
		S3=Ti-n-plated High-temperature			

						OPERATION		SCALE		Fit		 东莞市宇熙精密连接器有限公司 Dongguan Yuxi Electronic Co.,Ltd.		
						X.X	+0.25	UNIT		MM				
						X.XX	+0.20	SIZE	A4	DESIGN	庞国杰	PART NO	P220-1205A0AS087A1	
						X.XXX	+0.10							
						Angle	+13°	SHEET	1/1	CHECK		TITLE	2.0mm 双排针 2*5P 镀普金 PBT 180度 L=8.7/2.8 袋装	
REV	DATE	MODIFICATION DESCRIPTION			CHANGE	APPROVE	DIM	TOL	PROJ.		APPROVE		Customer No.	