








PRODUCT NO.	RoHS compliant
DSIC02TSGER	



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



- NOTES :
- 1>.Operating force:1000gf Max
 - 2>.Operating Temperature: -40° to+85°
 - 3>.Storage Temperature:: -40° to+85°
 - 4>.Mechanical Life:3000cycles minimum
 - 5>.Electrical Life:2000cycles 25mA 24VDC
2. PLATING:
- GOLD FLASH 1u"(min.) SOLDER TAIL,
3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION

DSIC XX I S G E R

[包装方式: I=管装 R=盒装]

[电镀层: B=镀锡3u" G=镀金3u" / 焊盘3u"-2u"]

[G=镀金 S=内金外镀]

[脚型: S脚 / J脚 / 0脚 / A脚 / Z脚]

[T=低粘附度 S=低粘附度 L=长推]

[产品代码: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]

Number	Part Name	Material	Finished	TOLERANCE UNLESS OTHERWISE SPECIFIED	INSPECTION COPY	FILE NO.
①	Actuator	UL94 VO	White	0 ± 0.25	0. ± 2"	DSIC02TSGER-A
②	Cover	UL94 VO	Black	.00 ± 0.15	.0 ± 1"	SIZE
③	Movble	Copper Alloy	3u"Gold	.000± 0.10	.00± 0.5"	UNIT SCALE
④	Terminal	Brass	1u"Gold			SHEET
⑤	Base	UL94 VO	Black			REV.
⑥	Terminal Contact	Brass	3u"Gold			
⑦	Myar	UL94 VO	0.05mm			

东莞市广德实业有限公司
Dongguan Kingtek Industrial Co., Ltd.

BY DSIC SERIES PITCH 2.54mm

PRODUCT FAMILY DSIC SERIES

DRAWING

CHECK

APPRO.