




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		图面升级整理图面	2024.08.21	阿树




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:7A AC/DC
额定电流: 7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:10mΩ Max
接触电阻: 10mΩ Max

X9396 T-B SN-U
① ② ③ ④ ⑤


- 1.Series No
- 2.Category:T-Terminal
- 3.Material:B-Beass
- 4.Plating:SN-Plated Tin
- 5.Special No:U-upgraded version



SECTION: A-A
SCALE:1:1



SECTION: B-B
SCALE:1:1



X9396T-BSN-U	Brass	AWG#24~16	X9396H
PART NO	Material	Wire Range	Suitable XKB Housing

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	3.96mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X9396T-BSN-U
APPROVED		SIZE: A4	DWG NO.: