








PCB.焊接图
PCB.WELDING DRAWING





- NOTES:
1. Rating: 12VDC 50mA
 1. 额定值: 12VDC 50mA
 2. Dielectric Strength: 250V AC
 2. 耐电压: 250V AC
 3. Contact Resistance: $\leq 100\text{m}\Omega$ Max
 3. 接触电阻: $\leq 100\text{m}\Omega$
 4. Insulation Resistance: $\geq 100\text{M}\Omega$
 4. 绝缘电阻: $\geq 100\text{M}\Omega$
 5. Operating Force: $160 \pm 50\text{gf}$
 5. 操作力: $160 \pm 50\text{gf}$
 6. Life: 50,000 times
 6. 寿命: 50,000 times
 7. Trip: $0.20 \pm 0.10\text{mm}$
 7. 行程: $0.20 \pm 0.10\text{mm}$



电路图
CIRCUIT DIAGRAM

6	Button 按钮	LCP	1	Black 黑色
5	Cover plate 盖板	SUS	1	
4	Dustproof film 防尘膜	Polyimide 聚酰亚胺	1	Aurantiacus 橙黄色
3	Shrapnel 弹片	SUS	2	Ag plating 镀银
2	Body 本体	LCP	1	Black 黑色
1	Card 卡件	Brass 黄铜	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注



A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:					
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP13721618				
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION		ISSUE	X	± 0.25									
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission								
				A		B		C		D		E		F		G