



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PBT

b.CONTACT:Mn Steel

(SURFACE PLATING: Ni100u"-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

a.CONTACT RESISTANCE: 100 MILLIOHMS MAX

b.INSULATION RESISTANCE: 100 MEGA OHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE MINUTE

d.OPERATING TEMPERATURE: -25℃ ~ +85℃

ORDERING INFORMATION

BS-24-A1AJ019

电池座系列

BS-24系列

DIP 90° TYPE

PLATING:

A-Au1U"

J-Ni100U"~120U"

K-Sn100U"~120U"

MATERIAL:

1A-PBT BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK





4A-LCP WHITE

4B-LCP BLACK

工程部

2019-07-04

LQ. HUANG



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	Mn Steel,T=0.50mm	Ni Plating
2	TERMINAL(+)	1	Mn Steel,T=0.50mm	Ni Plating
1	HOUSING	1	PBT	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2019-07-04
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2019-07-04
X.X :±0.25	X.X :±0.5°	APVD	XueShunYong	DATE	2019-07-04
X.XX :±0.20					
X.XXX :±0.10					
WEIGHT:		SCALE: 2:1	SIZE: A4	VIEW: ④ ①	TITLE:
SHEET 1 OF 1		UNIT: mm	REV.: A/0	OBJECT: MY	BS-2477-2 DIP (柱子加宽)
					PART NO.:
					BS-24-A1AJ019
					DRAW NO.:MY-CP-0206