


1. Rating:DC12V 50mA;
2. Contact Resistance:100m Ω Max;
3. Insulation Resistance:100M Ω Min;
4. Withstanding Voltage:AC250V For 1 Minute;
5. Life Cycle:100,000 Cycle Min;
7. Travel:0.25 \pm 0.1mm.

OperatingForce	A	100±30gf
	B	130±30gf
	C	160±30gf
	D	200±50gf
	E	250±50gf
	F	300±50gf



H	X
4.3	3.15
5.0	3.85
5.5	4.35
6.0	4.85
7.0	5.85
7.3	6.15
7.5	6.35
8.0	6.85
8.5	7.35
9.0	7.85
9.5	8.35
10.0	8.85
11.0	9.85
12.0	10.85
13.0	11.85
14.0	12.85
14.5	13.35
15.0	13.85
15.5	14.35
16.0	14.85
17.0	15.85

[illegible]