


REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			

Kinghelm®



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
- MATERIAL:
 - SEE TABLE
- ALL COMPONENTS ARE RoHS COMPLIANT.


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
			AS
②	接头	1代 IPEX端子	1
①	同轴线	RF 1.13黑色线,OD:1.13mm	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KHA-(RG1.13)-TX180-IPEX-221

0755-28190160

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2020-06-15			
	ENG.				
COMPUTER GENERATED IN SOLIDWORKS	MFG.				
DO NOT SCALE THIS DRAWING	Q.A.				
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		SIZE B	Number	REV A
			SCALE: Free		TYPE

CUSTOMER PIN:

