



RECOMMENDED P.C.B LAYOUT (TOP VIEW)
TOLERANCES: $\pm 0.10\text{mm}$

TOLERANCE TABLE

.0	± 0.30
.00	± 0.20
.000	± 0.05

SPECIFICATION

MATERIAL & FINISHES

INSULATOR: PBT GLASS FILLED UL94V-0

CONTACT: BRASS

SHELL : STEEL

PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL

Operation voltage: 250 VAC max.

Current rating: 3 Amps max.

Contact resistance: 15 mohms max.

Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55°C TO $+105^{\circ}\text{C}$

PARTS DIMENSION TABLE

	inner thread	4#40	
parts no.	DIM. a	DIM. b	inner thread
B,C	4.8	11.8	4#40
D,E	5.8	12.0	4#40

APPROVED:

DATE:

Ckmtw 深圳市灿科盟实业有限公司
CHANKLEMENT INDUSTRY CO., LTD

CHECKED:

DATE:

TITLE: DMRC-25S 母头 弯插 车针 铆合锁螺丝
全金 折弯7.2 带黑胶挡板

DRAWN:

DATE:

CLIENT P/N D-DMRC25PF-E001

LYF

2018-04-07

UNIT	mm	SCALE	free		
FILE NO.	Ckmtw-DMRC-0008			REV.	A