


Technical drawing of a 5-pin D-sub connector with dimensions in mm. The drawing shows a side view of the connector with dimensions: 2.6, 11.5±0.15, 0.9, 7.14, 13.56, 13.56, 13.56, 13.56, 69.7±0.3, 66.4±0.25, 3.2, Ø3, 1.7, and a callout 2.

[illegible]

Material Specification
Housing :Thermo-plastic, UL94V-0.

**Contact : Alloy Copper
Shield : Alloy Copper**
Please refer to the customer drawing when customer has specified



一般公差	品名:	RGH-5366-15 全塑 橙座

繪圖：吳素飛 日期：2022.6.6

日期: 2014.12.15

10~30	±0.20	料 号:	036618-80000010P126 (MR440/Z)
±0.15		材 質:	PTFE

蘇 無 山 蘇

图例:	单位: mm	比例: 1:1	纸张: A4	
页次:	1 of 1	版本:		

1 印 自 秘 得 不 用 部 有 限 公 司 电 子 瑞 州 温 供 面 图 该 修