









PCB.安装图



电路图



NOTES:

- 1.Rating:12VDC 50mA
- 1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC
- 2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max
- 3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 5.Working temperature: -40℃~+85℃
- 5.工作温度: -40℃~+85℃
- 6.Stroke: 0.50 ± 0.20mm
- 6.行程: 0.50±0.20mm
- 7.Waterproof grade: IP67
- 7.防水等级: IP67
- 8.Operating Force:160±60gf
- 8.操作力: 160±60gf
- 9.Life: 200,000 times
- 9.寿命: 200,000 次

5	Terminal 端子	H65	1	Ag plating 镀银
4	Pedestal 基座	PA6T	1	
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Button 按钮	RUBBER	1	White 白色
1	Cover 盖板	SUS	1	
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP14611635
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				