

PRODUCT NO.	1
DSHP06TJGET	RoHS compliant

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature:-40° to+85°
- 3>.Storage Temperature:-40° to+85°
- 4>.Electrical life Life:2000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:

GOLD FLASH 1u"~2u" SOLDER TAIL,
1u"~3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX T J G E T

[包装方式: T=管装 R=Reel]



[电镀层: E=接触部 1u"~3u" 焊脚部 1u"~2u"]

[G=镀全金 S=内镀金(接触部)外镀锡(焊脚部)]



[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]

[T=低推贴胶 S=低推不贴胶 L=长推]



[产品数: 02=2P 04=4P 08=8P 10=10P]



[Schematic]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	1u"~3u" Gold
④	Terminal	Brass	1u"~2u" Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1u"~3u" Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED	INSPECTION COPY
LINER	ANGLES
.0 ± 0.25	0. ± 2°
.00 ± 0.15	.0 ± 1°
.000± 0.10	.00± 0.5°
DESIGN	kathy
DRAWING	
CHECK	
APPRO.	

INSPECTION COPY
PROJECTION
03/20/12°

东莞市广督实业有限公司
DongGuan Kingtek Industrial Co., Ltd.
TITLE
BY DSHP SERIES PITCH 1.27mm
PRODUCT FAMILY DSHP SERIES
PRAT NO. DSHP06TJGET
FILE NO. DSHP06TJGET-A
SIZE A4
UNIT mm
SCALE 2 : 1
SHEET 1 OF 1
REV. A