






标 记
MARKECN编号/变更内容
ECN NO/DEFINITION修 改
REVISE日 期
DATE核 准
APPROVE

材料及电镀

1. 塑件主体: PA66

2. 焊 针: 黄铜, 镀镍

电气性能

额定电压: 300V

额定电流: 15A

接触电阻: 20mΩ (Max)

绝缘电阻: 500MΩ\DC500V

耐 电 压: AC2000V\1Min

机械性能

温度范围: -40℃ ~ +105℃

瞬时温度: +250℃ ,5秒

2	插针	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	接线端子
料 号 PART NO	HC-JXDZRC-5.08-9P

GENERAL TOLERANCES
(UNLESS SPECIFIED)比 例
SCALE

1:1



公差参数	未注明公差:
2-6P ±0.10 ±0.20	X. xxx ±0.10
7-12P ±0.20 ±0.30	X. xx ±0.20
13-16P ±0.25 ±0.40	X. x ±0.30
18-24P ±0.30 ±0.50	

X. xxx ±0.10
X. xx ±0.20
X. x ±0.30单 位
UNIT

MM

制 图
DRAW

AhYe

张 数
PART NO

1 OF 1

审 核
CHECKED

夏操云

版 本
REV

A

批 准
APPROVE

赵亮亮