

Ordering Information

F235-12 XX A0 C MU C 1

备注(Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing:PA9T+30%G. F UL94V-0, Color:Black

端子: 磷铜, 镍底30u", 表面镀普金

Contact: Phosphor, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 2 AMP

Raring Current:2 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.




温度范围: -40°C to $+105^{\circ}\text{C}$

Temperature Range: -40°C to $+105^{\circ}\text{C}$



Recommended P.C.B LAYOUT

General Tolerance ± 0.05



RoHS
COMPLIANT

客编：

注意事项

1. 带序号为必检尺寸, 带*为重点检验尺寸

				OPERATION		SCALE		Fit	 广东宇熙新能源技术有限公司 Guangdong Yuxi New Energy Technology Co., Ltd.		
				X.X	±0.25	UNIT		MM			
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2024.03.27	PART NO	P235-12XXA0CMUC1
				X.XXX	±0.10						
A0	2024.03.27	/	新版发行	Angle	±3°	SHEET	1/1	CHECK		TITLE	2.0排母3.5mm塑高 2*TP SMT:6.3 U型磷铜 塑宽=4.0 PA9T料 镀金管 管装
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL	PROJ.		APPROVE		Customer No.	