




+

+



技术要求 Specification:

- 1、材质 Material: Rubber shell:PA66 UL94V-2(0)
- 2、额定电流 Current rating: 5A max
- 3、额定电压 Voltage rating: 250V AC/DC
- 4、温度范围 Temperature range:-25°C to +105°C
- 5、接触电阻 Contact resistance: ≤15mΩ
- 6、绝缘电阻 Insulation resistance: ≥1000MΩ
- 7、耐压 Withstand voltage: 1000V AC/minute
- 8、适配的端子 Adaptable terminals: HX30002-RT
- 9、适配的插头 Adaptable plug: HX30002-P

未注 公差表 INTOLERANCE TABLE	差表 DRAWN BY	王鹏程	产品名称 PRODUCT NAME	插头 Plug Housing
≤3	± 0.1	审核 CHECKED BY 郑建银	产品型号 PRODUCT MODEL HXX-RF	43020
≤10	± 0.2	批准 APPROVED BY 沈才义	红星代号 HONGXING NO	HX30002-RF
≤20	± 0.3	日期 DATE 2020.04.08		
≤35	± 0.4			
≤50	± 0.5			
≤75	± 0.6	视图 VIEW	单位 UNIT 页码 SHEET 1/1	
≤100	± 0.8			
孔数 数目 NUMBER OF HOLES	2 4 6 8 10 12 14 16 18 20 22 24	∠ ANGLE	mm	

未注 公差表 INTOLERANCE TABLE											
≤3	± 0.1	审核 CHECKED BY 郑建银	产品型号 PRODUCT MODEL HXX-RF	43020							
≤10	± 0.2	批准 APPROVED BY 沈才义	红星代号 HONGXING NO	HX30002-RF							
≤20	± 0.3	日期 DATE 2020.04.08									
≤35	± 0.4										
≤50	± 0.5										
≤75	± 0.6	视图 VIEW	单位 UNIT 页码 SHEET 1/1								
≤100	± 0.8										
孔数 数目 NUMBER OF HOLES	2 4 6 8 10 12 14 16 18 20 22 24	∠ ANGLE	mm								

HXX®浙江红星电气有限公司
Zhejiang Hongxing Electrical Co., Ltd.