

Specifications

备注(Remark)

1. 材料(MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色:黑色.

Housing:PA9T+30%G.F UL94V-0, Color:Black

端子: 磷铜, 镍底30u"MIN, 表面镀金3u"MIN

Contact:Phosphor, 3u"MIN GOLD PLATING OVER ALL
30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Rating Current:1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance:20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.




Insulating Resistance:1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage:AC 500V/Minute.

温度范围: -40° C to+105° C

Temperture Range: -40° C to+105° C



Ordering Information

F321-12 14 A4 C MU B 2

NO. OF PINS
PER ROW
2-50P

Contact Plating
Full Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"

Seml-gold
B0=0.8u"
B1=1u"
B2=1.5u"
B3=2u"
B4=3u"
B5=5u"
B6=10u"
B7=15u"
B8=20u"
B9=30u"

INSULATOR MATERIAL:
B: PA6T
C: PA9T
D: LCP
S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

RoHS
COMPLIANT

客编:

注意事项

1. 带*为品质重点检验尺寸

OPERATION

SCALE

Fit

X.X ±0.25

UNIT

MM

X.XX ±0.20

SIZE

A4

X.XXX ±0.10

SHEET

1/2

Angle ±3°

CHECK

APPROVE

DIM TOL

PROJ.

APPROVE

Yxcon

东莞市宇熙精密连接器有限公司

www.yxcon.com

Dongguan Yuxi Electronic Co.,Ltd.

李官森2021.11.05

PART NO

F321-1214A4CMUB2

DESIGN

TITLE

1.27排母 H=2.1mm 2*14P SMT PA9T料 带内柱
镀金3U" CAP+2000/卷(KT)

APPROVE

Customer No.

新版发行

MODIFICATION DESCRIPTION

REV DATE SYMBOL

REV DATE SYMBOL