

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA9T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA9T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 1 AMP

Rating Current: 1 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.

Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.





温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C

Ordering Information

P315-12 05 A0 C M 072 B 1

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Semi-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
08: 0.8mm 10: 1.0mm 15: 1.5mm	2-50P	A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	B0=0.8U" B1=1U" B2=1.5U" B3=2U" B4=3U" B5=5U" B6=10U" B7=15U" B8=20U" B9=30U"	B: PA6T C: PA9T D: LCP		A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature						



RoHS
COMPLIANT

客编:

注意事项

1. 带*为品质重点检验尺寸

				OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co., Ltd.		
				X.X ±0.25	UNIT	MM			
				X.XX ±0.20	SIZE	A4	DESIGN	李官森2022.10.12	PART NO
				X.XXX ±0.10	SHEET	1/1	CHECK		TITLE
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	Angle ±3°	PROJ.	APPROVE			Customer No.
				DIM TOL					