







P.C.B LAYOUT(copper-sided view)



|           |             |
|-----------|-------------|
| Model NO. | PJ-3580A-6A |
| Schematic |             |

Rating:0.5A 30V DC  
 Contact Resistance:100 mΩ Max.  
 Operating temperature:-20℃~70℃  
 Operating force:3-20N  
 Operating Life:5,000cycles

|                |           |          |       |                                                                                            |            |                                                                                             |          |             |
|----------------|-----------|----------|-------|--------------------------------------------------------------------------------------------|------------|---------------------------------------------------------------------------------------------|----------|-------------|
| ②              | Terminal  | ——       | 5     | Phosphor bronze                                                                            | Ag Plating | ——                                                                                          |          |             |
| ①              | Housing   | ——       | 1     | Nylon                                                                                      | Black      | ——                                                                                          |          |             |
| ITEM           | PART NAME | TER'NO.  | QTY.  | MATERIAL                                                                                   | FINISHING  | REMARK                                                                                      |          |             |
| APPROVALS      |           |          | DATE  |  hro® |            |                                                                                             |          |             |
| DRAWN          | J.X.Zhang | 2018/8/1 |       |                                                                                            |            |                                                                                             |          |             |
| CHECKED        |           |          |       |                                                                                            |            |                                                                                             | TITLE:   | PHONE JACKS |
| APPROVALS      |           |          |       |                                                                                            |            |                                                                                             | PART NO. | PJ-3580A-6A |
| TOLERANCES ARE | 30~以上     | ±0.30    | ANGLE | UNIT: mm                                                                                   | SCALE: 1:1 | PROJ:  |          |             |
|                | 10~30     | ±0.20    |       |                                                                                            |            |                                                                                             |          |             |
|                | 5~10      | ±0.15    |       |                                                                                            |            |                                                                                             |          |             |
|                | ~ 5       | ±0.10    |       |                                                                                            |            |                                                                                             |          |             |
|                |           |          | ±2'   | DRAWING NO.                                                                                | ——         | SHEET 1 OF 1                                                                                |          |             |

|         |      |       |              |         |        |        |
|---------|------|-------|--------------|---------|--------|--------|
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
|         | A    |       | NEW          |         |        |        |