








P.C. BLAND DIMENSION





NOTES:

1. Rating: 12VDC 50mA
1. 额定值: 12VDC 50mA
2. Dielectric Strength: 250V AC
2. 耐电压: 250V AC
3. Contact Resistance: $\leq 100\text{m}\Omega$ Max
3. 接触电阻: $\leq 100\text{m}\Omega$
4. Insulation Resistance: $\geq 100\text{M}\Omega$
4. 绝缘电阻: $\geq 100\text{M}\Omega$
5. Working temperature: $-40^\circ\text{C} \sim +80^\circ\text{C}$
5. 工作温度: $-40^\circ\text{C} \sim +80^\circ\text{C}$
6. Stroke: $0.40 \pm 0.20\text{mm}$
6. 行程: $0.40 \pm 0.20\text{mm}$
7. Waterproof grade: IP67
7. 防水等级: IP67
8. Operating Force: $260 \pm 80\text{gf}$
8. 操作力: $260 \pm 80\text{gf}$
9. Life: 300,000 times
9. 寿命: 300,000 次



CIRCUIT DIAGRAM



5	Cover 盖板	SUS	1	
4	Plunger 垫片	RUBBER	1	Sky blue 天蓝色
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Pedestal 基座	PA6T	1	Black 黑色
1	Terminal 端子	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP144326265
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				