

MATERIAL

1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.

2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.

3. PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL

1.VOLTAGE RATING: 125 VAC RMS.

2.CURRENT RATING: 1.5 AMP.

3. CONTACT RESISTANCE: 40 MILLIOHMS MAX.

4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .

5.DIELECTRIC DIELECTRIC

RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL



1.DURRABILITY: 750 CYCLES MIN.

2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. OPERATION: $-40^{\circ}\sim+85^{\circ}$.

2. STORAGE: $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X'.:±3"	PART NO. RJ45-6051-8P	TITLE: RJ45 1x1 B数 全塑 DIP		
X.X:±0.25	X.X':±2"		MANUFACTURE DWG		
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN: Ethan			
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			