


P220-11 04 A0 B S 087 A 1

Temperture Range: -40° C to+105° C



| HEIGHT OF HOUSING | NO. OF PINS PER ROW | Contact Full of Gold              | Plating Semi-gold | INSULATOR MATERIAL: | LENGTH OF TERMINAL | PACKING        |
|-------------------|---------------------|-----------------------------------|-------------------|---------------------|--------------------|----------------|
| 10: 1.0mm         | 1-40P               | A0=0.8u"                          | B0=0.8U"          | B: PA6T             |                    | B: PE Bag      |
| 15: 1.5mm         |                     | A1=1u"                            | B1=1U"            | C: PA9T             |                    | B: Tape & Reel |
| 20: 2.0mm         |                     | A2=1.5u"                          | B2=1.5U"          | D: LCP              |                    | C: Tube        |
|                   |                     | A3=2u"                            | B3=2U"            |                     |                    | D: Tube+CAP    |
|                   |                     | A4=3u"                            | B4=3U"            |                     |                    | E: Tray        |
|                   |                     | A5=5u"                            | B5=5U"            |                     |                    |                |
|                   |                     | A6=10u"                           | B6=10U"           |                     |                    |                |
|                   |                     | A7=15u"                           | B7=15U"           |                     |                    |                |
|                   |                     | A8=20u"                           | B8=20U"           |                     |                    |                |
|                   |                     | A9=30u"                           | B9=30U"           |                     |                    |                |
|                   |                     | S1=Q di nary Ti n Pl ated         |                   |                     |                    |                |
|                   |                     | S2=Matte Ti n Pl ated             |                   |                     |                    |                |
|                   |                     | S3=Ti n-pl ated High-temper ature |                   |                     |                    |                |

1. 带\*为品质重点检验尺寸

|     |            |        |                          |             |       |                                                                                     |                                                                                                                                                                |               |                |
|-----|------------|--------|--------------------------|-------------|-------|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|----------------|
|     |            |        |                          | OPERATION   | SCALE | Fit                                                                                 |  <b>东莞市宇熙精密连接器有限公司</b><br>www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd. |               |                |
|     |            |        |                          | X.X ±0.25   | UNIT  |                                                                                     | MM                                                                                                                                                             |               |                |
|     |            |        |                          | X.XX ±0.20  | SIZE  | A4                                                                                  | DESIGN                                                                                                                                                         | 李官森2021.09.19 | PART NO        |
|     |            |        |                          | X.XXX ±0.10 |       |                                                                                     |                                                                                                                                                                |               |                |
| A0  | 2021.10.19 | /      | 新版发行                     | Angle ±3°   | SHEET | 1/1                                                                                 | CHECK                                                                                                                                                          |               | TITLE          |
| REV | DATE       | SYMBOL | MODIFICATION DESCRIPTION | DIM TOL     | PROJ. |  | APPROVE                                                                                                                                                        |               | Cust order No. |