








PCB Layout(Pattern side)



Circuit Diagram



NO.1	
PART NO	vigor
3	180±30
4	250±50
5	350±50

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	4	Brass(0.3t)	Plating silver	—
④	Contact	—	1	SUS	Plating silver	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	SUS	—	—
①	Keystoke	—	1	silica gel	Blue	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®		
DRAWN	LIUCAN	2022.2.16					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1157UG-B□SW-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
		±2'	DRAWING NO.		SHEET 1 OF		

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.