




材料及电镀

- 1. 塑件主体：PA66，
- 2. 焊 针：黄铜，镀镍


电气性能

额定电压：300V
额定电流：8A
接触电阻：20mΩ（Max）
绝缘电阻：500MΩ\DC1000V
耐 电 压：AC1500V\1Min

机械性能

温度范围：-40℃ ~ +105℃
瞬时温度：+250℃，5秒

2	插针	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE		接线端子																										
			料 号 PART NO		HC-JXDZRC-3.81-16P																										
GENERAL TOLERANCES (UNLESS SPECIFIED)			比 列 SCALE	1:1																											
<table border="1"><thead><tr><th colspan="4">公差参数</th></tr><tr><th>Poles</th><th>Dim</th><th>DimP</th><th>DimL</th></tr></thead><tbody><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td><td></td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td><td></td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td><td></td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td><td></td></tr></tbody></table> X. xxx ±0.15 X. xx ±0.25 X. x ±0.35 ANGULAR: X. xx° ±1° X. x° ±3° X. ° ±5°			公差参数				Poles	Dim	DimP	DimL	2-6P	±0.10	±0.20		7-12P	±0.20	±0.30		13-18P	±0.25	±0.40		19-24P	±0.30	±0.50		单 位 UNIT	MM	制 图 DRAW	AhYe	
			公差参数																												
			Poles	Dim	DimP	DimL																									
			2-6P	±0.10	±0.20																										
7-12P	±0.20	±0.30																													
13-18P	±0.25	±0.40																													
19-24P	±0.30	±0.50																													
张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云																												
版 本 REV	A	批 准 APPROVE	赵亮亮																												

