




- 材料及电镀
- ①. 螺 丝：M2.0，钢，镀锌，一字槽
  - ②. 塑件主体：PA66
  - ③. 夹 子：磷青铜，镀镍
  - ④. 方 盒：黄铜，镀镍
  - ⑤. 塑件盖板：PA66

电气性能

额定电压：300V 250V

额定电流：8A 7A

接触电阻：20mΩ (Max)

绝缘电阻：500MΩ\DC500V

耐 电 压：AC1500V\1Min

使用线径：28-16AWG 0.5-1.5mm<sup>2</sup>

机械性能

温度范围：-40℃ ~ +105℃

瞬时温度：+250℃ 5秒

扭 力：0.2N.m(2.04kgf.cm)

剥线长度：6-7mm

|     |     |      |       |     |
|-----|-----|------|-------|-----|
| 2   | 方盒  | 铜    | 镀镍    |     |
| 1   | 基座  | PA66 | 绿色    |     |
| 序 号 | 品 名 | 材 质  | 电镀/颜色 | 备 注 |



深圳市虹成电子有限公司

| 品 名<br>TITLE                                                                                                                                                                                                                                                                                                    |       | 接线端子            |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|-----------------|-------|------|-------|-----|-------|-------|-------|-------|-------|-------|-------|----------------|--------|-------|--------|-------|-------|-------------|----|
| 料 号<br>PART NO                                                                                                                                                                                                                                                                                                  |       | HC-JXDZK-3.5-5P |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                                                                                                                                                                                                                                        |       | 比 列<br>SCALE    | 1:1   |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| <table><tr><th colspan="3">公差参数</th></tr><tr><th>Poles</th><th>Dim</th><th>Dim L</th></tr><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td></tr></table> |       | 公差参数            |       |      | Poles | Dim | Dim L | 2-6P  | ±0.10 | ±0.20 | 7-12P | ±0.20 | ±0.30 | 13-18P         | ±0.25  | ±0.40 | 19-24P | ±0.30 | ±0.50 | 单 位<br>UNIT | MM |
| 公差参数                                                                                                                                                                                                                                                                                                            |       |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| Poles                                                                                                                                                                                                                                                                                                           | Dim   | Dim L           |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| 2-6P                                                                                                                                                                                                                                                                                                            | ±0.10 | ±0.20           |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| 7-12P                                                                                                                                                                                                                                                                                                           | ±0.20 | ±0.30           |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| 13-18P                                                                                                                                                                                                                                                                                                          | ±0.25 | ±0.40           |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| 19-24P                                                                                                                                                                                                                                                                                                          | ±0.30 | ±0.50           |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| <table><tr><td>X.xxx</td><td>±0.10</td></tr><tr><td>X.xx</td><td>±0.30</td></tr><tr><td>X.x</td><td>±0.50</td></tr><tr><td>X.xx*</td><td>±1*</td></tr><tr><td>X.x*</td><td>±3*</td></tr><tr><td>X.*</td><td>±5*</td></tr></table>                                                                               |       | X.xxx           | ±0.10 | X.xx | ±0.30 | X.x | ±0.50 | X.xx* | ±1*   | X.x*  | ±3*   | X.*   | ±5*   | 张 数<br>PART NO | 1 OF 1 |       |        |       |       |             |    |
| X.xxx                                                                                                                                                                                                                                                                                                           | ±0.10 |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| X.xx                                                                                                                                                                                                                                                                                                            | ±0.30 |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| X.x                                                                                                                                                                                                                                                                                                             | ±0.50 |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| X.xx*                                                                                                                                                                                                                                                                                                           | ±1*   |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| X.x*                                                                                                                                                                                                                                                                                                            | ±3*   |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
| X.*                                                                                                                                                                                                                                                                                                             | ±5*   |                 |       |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
|                                                                                                                                                                                                                                                                                                                 |       | 版 本<br>REV      | A     |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
|                                                                                                                                                                                                                                                                                                                 |       | 制 图<br>DRAW     | AhYe  |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
|                                                                                                                                                                                                                                                                                                                 |       | 审 核<br>CHECKED  | 夏操云   |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |
|                                                                                                                                                                                                                                                                                                                 |       | 批 准<br>APPROVE  | 赵亮亮   |      |       |     |       |       |       |       |       |       |       |                |        |       |        |       |       |             |    |

