

Specifications

备注 (Remark)

1. 材料 (MATERIAL)

胶芯: PA6T+30%G.F UL94V-0, 颜色: 黑色.

Housing: PA6T+30%G.F UL94V-0, Color: Black

四方针: 黄铜, 镍底30u"MIN, 表面镀普金

Contact: Brass, GOLD PLATING OVER ALL

30u" MIN NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.

温度范围: -40° C to +105° C



Temperture Range: -40° C to +105° C



Ordering Information

P125-11 40 A0 B S 210 A 2

HEIGHT OF HOUSING	NO. OF PINS PER ROW	Contact Full of Gold	Plating Serial-gold	INSULATOR MATERIAL	LENGTH OF TERMINAL	PACKING
15: 1.5mm 17: 1.7mm 20: 2.0mm 25: 2.54mm	1~40P	A0=0.8u" A1=1u" A2=1.5u" A3=2u" A4=3u" A5=5u" A6=10u" A7=15u" A8=20u" A9=30u"	B0=0.8u" B1=1u" B2=1.5u" B3=2u" B4=3u" B5=5u" B6=10u" B7=15u" B8=20u" B9=30u"	A: PBT B: PA6T C: PA9T D: LCP		A: PE Bag B: Tape & Reel C: Tube D: Tube+CAP E: Tray
		S1=Ordinary Tin Plated S2=Matte Tin Plated S3=Tin-plated High-temperature				



RoHS
COMPLIANT

1. 带*为品质重点检验尺寸

				OPERATION	SCALE	Fit	Yxcon 东莞市宇熙精密连接器有限公司			
				X.X	±0.25	UNIT	MM	www.yxcon.com	Dongguan Yuxi Electronic Co., Ltd.	
				X.XX	±0.20	SIZE	A4	DESIGN	李官森2021.12.17	PART NO
				X.XXX	±0.10	SHEET	1/1	CHECK		TITLE
A0	2021.12.17	/	新版发行	Angle	±3°	PROJ.	1/1	APPROVE		2.54排针 1*40P L=21.0/3.0 180度
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	DIM	TOL					PA6T 镀普金 100/袋
									Customer No.	