










PCB.WELDING DRAWING
PCB.焊接图



CIRCUIT DIAGRAW
电路图



NOTES:

- 1.Rating voltage: 50mA DC12V
- 1.额定电压: 50mA DC12V
- 2.Contact Resistance: ≤100mΩ Max
- 2.接触电阻: ≤100mΩ
- 3.Operating Force: 260±50gf
- 3.操作力: 260±50gf
- 4.Insulation Resistance: ≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 6.Life: 50,000 times
- 6.寿命: 50,000 times
- 7.Travel: 0.20±0.1mm
- 7.行程: 0.20±0.1mm
- 8.Operating Temperature: -20℃~80℃
- 8.使用温度: -20℃~80℃

5	Push-button 按钮	LCP	1	Black 黑色
4	Blind flange 盖板	Brass	1	Ag plating 镀银
3	Shrapnel 弹片	SUS	2	Ag plating 镀银
2	Noumenon 本体	LCP	1	white 白色
1	Card 卡件	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP13322632	
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
						X	± 0.25					
REV	DATE	REVISION	DESCRIPTION		ISSUE		ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
A		B		C		D		E		F		G

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission