







SCHEMATIC (NON-SHORTING)

P.C.B LAYOUT
BOTTOM VIEW

H=XXmm

8					TOLERANCE UNLESS SPECIFIED							
7												
6	SPRING PLATE	SUS Δ	1	NATURAL	UP TO 5mm: ± 0.1	ANGULAR	A1	2023.3.25	更新图纸 Δ	MLQ		
5	CONTACT CLIP	PHOSPHOR BRONZE	2	Ag CLAD	ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS	BY	APPD	
4	TERMINAL	BRASS STRIP	6	Ag PLATED	TITLE: SLIDE SWITCH			UNIT : MM	ROHS	DWN		
3	BASE	PHENOLIC RESIN	1	NATURAL	MODEL: SS-22D03MG3-001			SCALE: 1:1	COMPLIANT	CHK'D		
2	FRAME	STEEL STRIP	1	Ni PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司			APPD				
1	KNOB	PA9T	1	BLACK								
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL:		REV :A1	