






7		8	
REV.	ECN NO.	REVISED	DATE



技术要求:

- 1、截断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;
- 3、带‘*’尺寸为重点管控尺寸;

1	TERMINAL	1	SUS304, T=0.5MM	Ni-PLATING
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2023-01-07
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2023-01-07
X.X :±0.25	X.X :±0.5°	APVD	XueShunyong	DATE	2023-01-07
X.XX :±0.20		WEIGHT:	SCALE:5:1	SIZE: A4	VIEW:
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: 7号电池弹片正负极连片014 Ni	
				PART NO.: MY-AAA-14-J	
				DRAW NO.:WD-CP-0240	