






CAD FILE :



RATING: DC 50V 0.3A

|     |             |                       |      |                               |                                                   |       |      |              |           |       |  |
|-----|-------------|-----------------------|------|-------------------------------|---------------------------------------------------|-------|------|--------------|-----------|-------|--|
| 8   |             |                       |      |                               | TOLERANCE<br>UNLESS SPECIFIED                     |       |      |              |           |       |  |
| 7   |             |                       |      |                               |                                                   |       |      |              |           |       |  |
| 6   |             |                       |      |                               | WITHIN:1.5mm±0.1mm<br>OVER :1.5mm±0.2mm           |       |      |              |           |       |  |
| 5   | SPRING      | SUS                   | 1    | TEMPER                        |                                                   | ISSUE | DATE | DESCRIPTIONS |           | APPD. |  |
| 4   | CAM STICK   | SUS                   | 1    | NATURAL                       | TITLE : Slide switch series                       |       |      | UNIT :MM     | DRWG NO.: |       |  |
| 3   | INSERT CASE | NYLON+F.G/BRASS STRIP | 1    | GREY/Ag PLATED OVER Ni PLATED | MODEL: SS22D07VG2                                 |       |      | SCALE:5:1    | DWN       |       |  |
| 2   | COVER       | POM                   | 1    | BLACK/WHITE                   |                                                   |       |      |              | CHK'D     |       |  |
| 1   | INSERT KNOB | POM/PBS C5210R-EH     | 1    | WHITE/Ag CLAD                 |                                                   |       |      |              | APPD.     |       |  |
| NO. | PART NAME   | MATERIAL              | Q'TY | FINISHING                     | 深圳市逸致电子有限公司<br>Shenzhen Yizhi Electronics Co.,LTD |       |      |              |           |       |  |