



SPECIFICATIONS

Current rating: 2A AC/DC

Voltage rating: 250V AC/DC

Contact resistance: 20mΩ max.

Withstand voltage: 800V AC/min

Insulation resistance: 1000MΩ/min.

Temperature range: -25°C~+85°C

Applicable PC board thickness: 0.031"~0.063"(0.8~1.6)

Material:

Post: Brass. Tin plated

Base: PA66, UL94V-0

Poles	Part No	Dimension mm	
		A	B
2	2001S-2P	2.0	6.0
3	2001S-3P	4.0	8.0
4	2001S-4P	6.0	10.0
5	2001S-5P	8.0	12.0
6	2001S-6P	10.0	14.0
7	2001S-7P	12.0	16.0
8	2001S-8P	14.0	18.0
9	2001S-9P	16.0	20.0
10	2001S-10P	18.0	22.0
11	2001S-11P	20.0	24.0
12	2001S-12P	22.0	26.0
13	2001S-13P	24.0	28.0
14	2001S-14P	26.0	30.0
15	2001S-15P	28.0	32.0

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD					
CHECKED:	DATE:	TITLE: 2001S-3P 带扣 米黄色					
DRAWN: LYF	DATE: 2014-08-08	PART. NO.	W-2004S03P-B200				
		UNIT	mm	SCALE	free	☉	☐
		FILE NO.	Ckmtw-2001-0007		REV.	A	KL00