






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Recommended PCB Layout
(Tolerance: ± 0.05)



1. Material:
- 1.1 Housing: **PBT** UL94V-0 Black.
 - 1.2 Contact :Phosphor Bronze(C5210),Gold plated on contact area **30u"**.
 - 1.3 Input Terminal : Brass(C2680).
 - 1.4 Metal shielding:Copper alloy with Nickel plated(C2680).
2. Environmental requirements:
- 2.1 Lead-free process,compliant RoHS.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.: ± 0.35	X': $\pm 3'$	PART NO. RJ45-4054-8P	TITLE: 5921 1x1无弹左绿右黄 B3.05 DIP 100 μ 30u" PBT		
X.X: ± 0.25	X.X': $\pm 2'$				
X.XX: ± 0.15	X.XX': $\pm 1'$				
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava	SCALE N:A	SHEET 1/1

