





电话：0769-82310511-867
邮箱：hooya89@hooya.hk
V：hooya89



SECTION A-A
(插针规格: $\phi 3.0$)



SECTION A-A
(插针规格: $\phi 2.0$ & $\phi 2.5$)



DC MATE PLUG

PIN	ø2.0	ø2.5	ø3.0
DIM A	ø6.3±0.05	ø6.3±0.05	ø6.55±0.0
DIM B	ø2.05 ^{+0.10} _{-0.00}	ø2.55 ^{+0.10} _{-0.00}	ø3.05 ^{+0.10} _{-0.00}

Model No.	DC-062	DC-062-1
Schematic		
CIRCUIT DIAGRAM		

					TOLERANCE UNLESS SPECIFIED									
6	Shunt Terminal③	BRASS	1	Ag/Sn-PLATED	UP TO 5mm:±0.1	ANGULAR	1							
5	Tip spring②	SUS	1	Ag/Sn-PLATED	ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS			BY	APPD	
4	Center pin terminal①	BRASS	1	Ag/Sn-PLATED	TITLE:DC JACK				UNIT : MM	ROHS	DWN			
3	Center pin	BRASS	1	Sn PLATED	MODEL:DC-062-2.0				SCALE: 3:1	COMPLIANT	CHK'D			
2	Cover	PBT	1	BLACK	 HAOYU(HONGKONG)LIMITED 皓 宇(香 港)有 限 公 司							APPD		
1	Housing	PBT	1	BLACK								PRO.AGL:	 	
NO.	PART NAME	MATERIAL	QTY	FINISHING										