






PRODUCT NO.	RoHS compliant
DSHP02TUGER	



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3μt Gold
④	Terminal	Brass	1μt Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3μt Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED			INSPECTION COPY	
LINER	ANGLES		PROJECTION	
0 ± 0.25	0. ± 2°		BY DSHP SERIES PITCH 1.27mm	
100 ± 0.15	.0 ± 1°		PRODUCT FAMILY DSHP SERIES	
1000 ± 0.10	.00 ± 0.5°		PRAT NO. DSHP02TUGER	
DESIGN			FILE NO. DSHP02TUGER-A	
DRAWING			SIZE UNIT SCALE SHEET REV.	
CHECK			A4 mm 2 : 1 10F-1 A	
APPRO.				

NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations



2. PLATING:

GOLD FLASH 1u"(min.) SOLDERAL,
3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX T J G E R

[Schematic]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

东莞市广智实业有限公司
Dongguan Kingtek Industrial Co., Ltd.