


CIRCUIT DIAGRAM



- 1.Rating:12VDC 50mA
- 1.额定值: 12VDC 50mA
- 2.Dielectric Strength:250V AC
- 2.耐电压: 250V AC
- 3.Contact Resistance:≤100mΩ Max
- 3.接触电阻: ≤100mΩ
- 4.Insulation Resistance:≥100MΩ
- 4.绝缘电阻: ≥100MΩ
- 5.Working temperature: -40℃~+80℃
- 5.工作温度: -40℃~+80℃
- 6.Stroke: 0.40 ± 0.20mm
- 6.行程: 0.40±0.20mm
- 7.Waterproof grade: IP67
- 7.防水等级: IP67
- 8.Operating Force:260±80gf
- 8.操作力: 260±80gf
- 9.Life: 300,000 times
- 9.寿命: 300,000 次

5	Cover 盖板	SUS	1	
4	Plunger 垫片	RUBBER	1	Sky blue 天蓝色
3	Shrapnel 弹片	SUS	1	Ag plating 镀银
2	Pedestal 基座	PA6T	1	Black 黑色
1	Terminal 端子	Brass	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:			
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP142226265			
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD							
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						± 0.25		
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission							
					A			D		E		F		G