







REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.11.18	阿树





U262-24XN-3BVC82

1:AU 1U"
2:AU 3U"
4:AU 15U"
5:AU 30U"

1:PBT
2:PA6T
3:PA9T
4:LCP

1:WITH
2:WITHOUT

W:WHITE
B:BLACK



SPECIFICATION:

- Material
Housing Material:High temperature thermoplastic
Contact Terminal:High Grade Copper Alloy
Merallic Shell:Stainless Steel
Inner Ground Cover Shell:Stainless Steel
Mid Plate:Stainless Steel
- Mechanical:
2.1.Mating force:5-20Nf;
2.2.Unmating force:Initial:8-20Nf;Final:6-20Nf;
2.3.Durability:10000 Cycles;
- Electrical:
3.1.Current Rating:3A
3.2.Voltage Rating:20V Max.;
3.3.Dielectric Withstanding volage:100Vac,60S,10mA;
3.4.Contact resistance:40m Ohms Max.;
3.5.Insulation Resistance:100M Ohms Min.;
- Environmental:
4.1.Operating temperature:-30°C~+80°C;
4.2.Salt Spray Test:24H Min.(No oxidation or rust);

RECOMMENDED P.C.B LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:	MODEL TYPE: USB TYPE C -24PIN PLUG
CHECKED		UNIT: mm/in	PART NO.: U262-24XN-3BVC82
APPROVED		SIZE: A4	DWG NO.: