












SPECIFICATIONS 规格:

1. ELECTRICAL CHARACTERISTICS 电气特性:

- 1.1. RATING 电流: 3A;
- 1.2. CONTACT RESISTANCE 接触电阻: 30 mΩ MAX.(INITIAL);
- 1.3. DIELECTRIC WITHSTANDING 耐电介质: 100V AC MIN.;
- 1.4. INSULATION RESISTANCE 绝缘电阻: 100MΩ MIN.;
2. DURABILITY 耐用性: 10,000 CYCLES MIN.;
3. INSERTION FORCE 插入力: 5-20N;
4. EXTRACTION FORCE 拔出力: 6-20N;
5. WATER PROOFNESS 防水: THIS PRODUCT IS BASED ON IPX6.
6. PLUG INTERFACE DIMENSIONS COMFORM TO USB2.0 SPEC.

U262-06XN-5BF621

1:Au 1U"
3:Au 3U"
5:Au 10U"

W:WHITE
B:BLACK
1:PBT
2:PA6T
3:PA9T
4:LCP
5:PA10T

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

3	Shell	1	SUS304R-1/2H Ni PlatingT=0.25mm	
2	Contact	6	Phosphor bronze C5191R-EH Au/Ni Plating T=0.20mm	
1	Housing	1	PA10T (G.F30%)	
ITEM	PART NAME	Q'TY	FINISH	NOTE

广东星坤科技股份有限公司

日期

文件工程章

DESCRIPTION

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

DATE

REVISED

APPROVED

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:	3.1 TYPE C
DWN		VIEW:	PART NO.:	
CHKD		UNIT: mm/in	DWG NO.:	U262-06XN-5BF621
APPD		SIZE: A4	WEIGHT	SHEET
				1/1
			REVISION	A0