


Circuit Diagram



NOTE:  
Rating: DC 12V 50mA  
Travel: 0.2±0.1mm  
Life: 100,000 Cycles

NO.1	
PART NO	NOTE
3	160±40
4	250±50

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	4	Phosphor bronze	Plating silver	—
④	Contact	—	2	F.Ag/SUS	—	—
③	Base	—	1	LCP	White	—
②	Cover	—	1	Phosphor bronze	Plating silver	—
①	Keystoke	—	1	LCP	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE				
DRAWN	LIUCAN	2024.6.23				
CHECKED				TITLE:	TACT SWITCHS	
APPROVALS				PART NO.	K2-1805ST-A□DW-□□	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			PROJ:
DESCRIPTION.		5~10	±0.15	±2°	DRAWING NO.	SHEET 1 OF 1
		~ 5	±0.10			

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.