




SPECIFICATION

MATERIAL & FINISHES

INSULATOR: PBT GLASS FILLED UL94V-0

CONTACT: BRASS

SHELL : STEEL

PLATING : CONTACT GOLD FLASH PLATED

ELECTRICAL

Operation voltage: 250 VAC max.



Current rating: 3 Amps max.

Contact resistance: 15 mohms max.


Insulation resistance: 3000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1000 VAC / minute

Operating temperature: -55°C TO +105°C



PARTS DIMENSION TABLE			
	b		
	a		
	inner thread		
	4#40		
parts no.	DIM. a	DIM. b	inner thread
F,G	5.0	10.0	4#40
H,J	4.8	11.8	4#40
I,K	5.8	12.0	4#40



RECOMMENDED P.C.B LAYOUT (TOP VIEW)

TOLERANCE TABLE

.0 ±0.30

.00 ±0.20

.000 ±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DMSC-50P 三排 公头 直插 车针 全金 铆合锁螺丝			
DRAWN: LYF	DATE: 2018-04-07	CLIENT P/N		D-DMSC50PM-F001	
		UNIT	mm	SCALE	free
		FILE NO.		Ckmtw-DMSC-0005	REV. A